## FCM-Z7/0ZD005



FDF Fiber Termination Panel, 144 SC/UPC, singlemode, 8 in x 23 in, putty white, pre-terminated with IFC cable, 5 meters, Stub tail at far end

#### Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with IFC cable

Product Series FDF

## General Specifications

**Functionality** Patching

**Application** Used in rear-load FDF-style frames only

Body Style Symmetrical

Cable Exit Location Upward

Cable Stub Type IFC, stranded
Color Putty white

Color, front
Putty white

Growth Configuration
Interface, front
SC/UPC
Interface, rear
Stub tail

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 23 in
Rack Units 4.57
Shelf Movement Fixed
Total Ports, quantity 144

### **Dimensions**

 Height
 203.2 mm | 8 in

 Width
 584.2 mm | 23 in

 Depth
 304.8 mm | 12 in

**COMMSCOPE®** 

# FCM-Z7/0ZD005

**Cable Length** 5 m | 16.404 ft

Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

**Fiber Mode** Singlemode

**Environmental Specifications** 

**Operating Temperature**  $-40 \,^{\circ}\text{C}$  to +70  $^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

