FCM-ZL/OZD092



FDF Fiber Termination Panel, 144 SC/APC, singlemode, 8 in x 23 in, putty white, pre-terminated with IFC cable, 92 meters, Stub tail at far end

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with IFC cable

Product Series FDF

General Specifications

Functionality Patching

Application Used in rear-load FDF-style frames only

Body Style Symmetrical

Cable Exit Location Upward

Cable Stub Type IFC, stranded

Calor Putty white

ColorPutty whiteColor, frontPutty whiteGrowth ConfigurationFully loadedInterface, frontSC/APCInterface, rearStub tail

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 23 in
Rack Units 4.57
Shelf Movement Fixed
Total Ports, quantity 144

Dimensions

 Height
 203.2 mm | 8 in

 Width
 584.2 mm | 23 in

 Depth
 304.8 mm | 12 in

COMMSCOPE®

FCM-ZL/OZD092

Cable Length 92 m | 301.837 ft

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to +70 $^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

