FL1-H7/02HD1-153



FL1000 Fiber Wall Box, 2-door, singlemode SC/UPC, 24 ports, with Indoor/outdoor cable, stub at far end, 153 meters

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

Regional AvailabilityNorth AmericaProduct TypeFiber wall boxProduct SeriesFI 1000

General Specifications

Application Patching | Splicing

Adapter Packs Included, quantity 4

Adapters, quantity 24

Cable Clamps, quantity 1

Cable Color Black

Cable Entry Location Bottom left | Bottom right | Top left | Top right

Cable Type Indoor/outdoor - Stranded

Color Putty white

Door, quantity 2

Front Door Type Single hinged
Growth Configuration Fully loaded
Interface SC/UPC
Mounting Wall
Total Fibers, quantity 24

Total Ports, quantity 24


Dimensions

Cable Length 153 m | 501.969 ft



FL1-H7/02HD1-153

Outline Drawing



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA type 12

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

COMMSCOPE®

FL1-H7/02HD1-153

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

