

LSX-LL/OWX018



LSX Fiber Term Panel 8 Ru, 288 - SC/APC, Singlemode IFC Ribbon, 18 Meters, Far end connection Stub

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with OSP cable
Product Series	LGX

General Specifications

Functionality	Patching
Application	Used in LSX-style frames only
Cable Exit Location	Upward
Cable Stub Type	IFC, ribbon
Color	Putty white
Color, front	White
Growth Configuration	Fully loaded
Interface, front	SC/APC
Interface, rear	Stub tail
Rack Type	EIA 23 in
Rack Units	8
Shelf Movement	Fixed
Total Ports, quantity	288

Dimensions

Height	279.4 mm 11 in
Width	482.6 mm 19 in
Depth	304.8 mm 12 in

LSX-LL/OWX018

Cable Length 18 m | 59.055 ft

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

