

# F1A-HMDF-1M5-P



FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Female , 1.5M

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

Product Type	SureFlex® Premium, static PIM
Product Brand	HELIAX®   SureFlex®
Product Series	FSJ1-50A

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	7-16 DIN Female
Specification Sheet Revision Level	A

## Dimensions

Length	1.5 m   4.921 ft
Nominal Size	1/4 in

## Electrical Specifications

3rd Order IMD	-107 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.152	23.02
1700–2200 MHz	1.152	23.02
2200–2700 MHz	1.152	23.02

## Jumper Assembly Sample Label

# F1A-HMDF-1M5-P



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system