

RCP-4ZBPU022900



RapidFiber® Termination Panel, 288-Position 4RU, singlemode, LC/APC to stub, 229m

Product Classification

| | |
|------------------------------|-------------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel, with rapid cable |
| Product Brand | RapidFiber® |
| Product Series | RCP |

General Specifications

| | |
|----------------------------------|---|
| Functionality | Patching |
| Body Style | Symmetrical |
| Cable Exit Location | Rear, left side |
| Cable Stub Type | IFC, stranded |
| Color | Putty white |
| Door Type, front | Hinged Slide latch Transparent |
| Growth Configuration | Fully loaded |
| Interface, front | LC/APC |
| Interface, rear | Stub tail |
| Patch Cord Entry Location | Front, left side Front, right side |
| Rack Type | EIA 19 in EIA 23 in |
| Rack Units | 4 |
| Shelf Movement | Sliding |
| Total Fibers, quantity | 288 |
| Total Ports, quantity | 288 |
| Transmission Standards | IEC 60794-2 ISO/IEC 11801 TIA/EIA-568-B.3 |

Dimensions


| | |
|---------------|-----------------|
| Height | 177.8 mm 7 in |
|---------------|-----------------|

RCP-4ZBPU022900

Width 482.6 mm | 19 in

Depth 381 mm | 15 in

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A2/B2

RCP-4ZBPU022900

Environmental Specifications

| | |
|--------------------------------|--|
| Operating Temperature | -5 °C to +55 °C (+23 °F to +131 °F) |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Relative Humidity | 5%–85%, non-condensing |
| Qualification Standards | NEBS Level 3 Telcordia GR-1435 Telcordia GR-326 Telcordia GR-409 UL 1863 |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Included Products

| | | |
|--------------------------------|---|--|
| 760245201 P-024-MP-8V-F30YL | – | Fiber indoor cable, Plenum for MPO Light Duty Patchcords, 24 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color |
|--------------------------------|---|--|