

# FPCRD-SPLC-P-1.4M

---

Fiber Optic Patch Cord, Duplex, Singlemode, LC/UPC to LC/UPC, yellow, 1.4 m

## Product Classification

|                              |                               |
|------------------------------|-------------------------------|
| <b>Regional Availability</b> | Latin America   North America |
| <b>Product Type</b>          | Fiber patch cord, duplex      |
| <b>Product Series</b>        | FPC                           |

## General Specifications

|                               |        |
|-------------------------------|--------|
| <b>Connector A, quantity</b>  | 2      |
| <b>Color, boot A</b>          | Blue   |
| <b>Color, connector A</b>     | Blue   |
| <b>Connector B, quantity</b>  | 2      |
| <b>Color, boot B</b>          | Blue   |
| <b>Color, connector B</b>     | Blue   |
| <b>Interface, Connector A</b> | LC/UPC |
| <b>Interface, Connector B</b> | LC/UPC |
| <b>Jacket Color</b>           | Yellow |
| <b>Total Fibers, quantity</b> | 2      |

## Dimensions

|   |                  |
|---|------------------|
| <b>Cable Assembly Length Range (m)</b>  | 1 – 999          |
| <b>Cable Assembly Length Range (ft)</b> | 1 – 999          |
| <b>Cord Length</b>                      | 1.4 m   4.593 ft |
| <b>Diameter Over Jacket</b>             | 2 mm   0.079 in  |

## Optical Specifications

|   |                      |
|---|----------------------|
| <b>Fiber Mode</b>                           | Singlemode           |
| <b>Fiber Type</b>                           | G.657.A2, TeraSPEED® |
| <b>Insertion Loss, maximum, connector A</b> | 0.3 dB               |
| <b>Insertion Loss, maximum, connector B</b> | 0.3 dB               |
| <b>Return Loss, minimum, connector A</b>    | 55 dB                |
| <b>Return Loss, minimum, connector B</b>    | 55 dB                |

# FPCRD-SPLC-P-1.4M

---

## Environmental Specifications

**Environmental Space** Plenum

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

