

# IFC-E/EA015

---

Fiber Optic Intra Facility Fiber Cable, OS2, SC/APC to SC/APC, yellow, 15 m

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	Fiber distribution cable assembly
<b>Product Series</b>	IFC

## General Specifications

<b>Color, boot A</b>	Green
<b>Color, boot B</b>	Green
<b>Color, connector A</b>	Green
<b>Color, connector B</b>	Green
<b>Connector A, quantity</b>	12
<b>Connector B, quantity</b>	12
<b>Interface, Connector A</b>	SC/APC
<b>Interface, Connector B</b>	SC/APC
<b>Jacket Color</b>	Yellow
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Cord Length</b>	15 m   49.213 ft
--------------------	------------------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	OS2
<b>Insertion Loss, maximum, connector A</b>	0.35 dB
<b>Insertion Loss, maximum, connector B</b>	0.35 dB
<b>Return Loss, minimum, connector A</b>	65 dB
<b>Return Loss, minimum, connector B</b>	65 dB

## Environmental Specifications

<b>Environmental Space</b>	Riser
----------------------------	-------

# IFC-E/EA015

---

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

REACH-SVHC

ROHS

### Classification

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

