

# MIFC-9/02C050-NGF

---

Fiber Optic Intra Facility Cable, Multimode, OM2, SC/UPC to Stub, orange, 50 m

**OBSOLETE**

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	Fiber distribution cable assembly
<b>Product Series</b>	IFC

## General Specifications

<b>Color, boot A</b>	Beige
<b>Color, connector A</b>	Beige
<b>Connector A, quantity</b>	48
<b>Connector B, quantity</b>	0
<b>Interface, Connector A</b>	SC/UPC
<b>Interface, Connector B</b>	Unterminated
<b>Jacket Color</b>	Orange
<b>Total Fibers, quantity</b>	48

## Dimensions

<b>Cord Length</b>	50 m   164.042 ft
--------------------	-------------------

## Optical Specifications

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	OM2

## Environmental Specifications

<b>Environmental Space</b>	Riser
----------------------------	-------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

# MIFC-9/02C050-NGF

---

**Agency**

CHINA-ROHS  
REACH-SVHC  
ROHS

**Classification**

Above maximum concentration value  
Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)  
Compliant/Exempted

