760245548 | ODF-SPLCAB-24



UMSC (Universal Mounted Splice Cabinet) with up to 6912 fiber splices capacity (Rollable ribbon cables), exit up, gray

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Universal Mounted Splice Cabinet

Product Series Flex Frame

General Specifications

AccessFrontCable Entry LocationTopCable Exit LocationTopColorGray

Growth Configuration Unloaded

Mounting Back to Back | Rack, EIA 19 in | Rack, EIA 23 in | Wall

Splice Trays Included, quantity 0

Splicing Capacity NoteUp to 6912 Rollable Ribbon Splices

Splicing Capacity, maximum 6912

Dimensions

 Height
 1,747.3 mm | 68.791 in

 Width
 443 mm | 17.441 in

 Depth
 287.9 mm | 11.335 in

Environmental Specifications

Environmental Space Indoor

