




MATERIAL ID	DESCRIPTION
760161380	imVision CONTROLLER

NOTES:

- SEE SYSTIMAX CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR/PKG.
- SEE SYSTIMAX CATALOG FOR COMPLETE LIST OF PARTS RELATED TO THE USE OF THIS PRODUCT.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- * 4. THE DIMENSION IS ADJUSTABLE TO 2.00[50.8], 4.75[120.6] AND 7.14[181.3].
- PART INCLUDES:
 - (1) ASSEMBLY, imVision, CONTROLLER DISPLAY WITH MOUNTING BRACKET
 - (1) ASSEMBLY, imVision, CONTROLLER ASSY
 - (4) BAR, imVision, CABLE MANAGEMENT BAR
 - (1) BOLT, DISPLAY MOUNTING
 - (1) TIE WRAP
 - (1) POWER SUPPLY, ImVision
 - (1) CLIP, WIRE
 - (1) RACK MOUNTING SCREWS, NO. 12, Dog Point Screw w/ Washers, Bag of 4
 - (1) PANEL BUS ASSY, W/RACEWAY HOUSING
 - (1) CABLE ASSEMBLY, JUMPER, NGIC
 - (1) KNOB, ADJUSTMENT
 - (2) BRACKET, imVision, MOUNTING CLAMP
 - (1) CABLE ASSEMBLY, USB A TO USB MICRO B
 - (1) CABLE ASSY, imVision CONTROLLER, GROUNDING
 - (1) NUT/WASHER ASSY, #6-32 SS
 - (5) SCREW, PHMS, SS, ACR2, STAP, 6-32UNC X 3/8 LONG
 - (1) CABLE, CONNECTORIZED, GS8E GRAY, 7 FEET



imVision CONTROLLER	
COMMSCOPE, INC OF NORTH CAROLINA	
SYSTIMAX® SOLUTIONS	
DRAWN BY CZ	DJ
DATE 01/30/2012	DWG NO 760161380

REV	DATE	ECR	DESCRIPTION	APPROVED BY
1	01/30/12		INITIAL ISSUE	CZ