

## IR12SP 2-port Single Gang Stainless Steel Industrial Faceplate

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Faceplate kit

### General Specifications

<b>ANSI/TIA Category</b>	5e   6   6A
<b>Application</b>	Used with M Series modular information outlet
<b>Color</b>	Silver
<b>Mounting</b>	Flush
<b>Total Ports, quantity</b>	2

### Dimensions

<b>Height</b>	114.3 mm   4.5 in
<b>Width</b>	69.85 mm   2.75 in
<b>Receptacle Opening</b>	27.94 mm   1.1 in

### Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

### Environmental Specifications

<b>Operating Temperature</b>	-25 °C to +85 °C (-13 °F to +185 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Qualification Standards</b>	IEC 60529: 2001, IP44
<b>Safety Standard</b>	UL   cUL

### Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value

# 760043000 | IR12SP

---

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

