

# 760043018 | IR24SP

---

## IR24SP 4-port Double Gang Stainless Steel Industrial Faceplate

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Faceplate kit
<b>Product Series</b>	M Series

### General Specifications

<b>ANSI/TIA Category</b>	5e   6   6A
<b>Application</b>	Used with M Series modular information outlet
<b>Color</b>	Silver
<b>Mounting</b>	Flush
<b>Total Ports, quantity</b>	4

### Dimensions

<b>Height</b>	114.3 mm   4.5 in
<b>Width</b>	115.824 mm   4.56 in
<b>Receptacle Opening</b>	27.94 mm   1.1 in

### Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

### Environmental Specifications

<b>Operating Temperature</b>	-25 °C to +85 °C (-13 °F to +185 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Qualification Standards</b>	IEC 60529: 2001, IP44
<b>Safety Standard</b>	UL   cUL

### Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

### Regulatory Compliance/Certifications

# 760043018 | IR24SP

---

**Agency**

CHINA-ROHS  
ISO 9001:2015  
REACH-SVHC  
ROHS  
UK-ROHS

**Classification**

Below maximum concentration value  
Designed, manufactured and/or distributed under this quality management system  
Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)  
Compliant  
Compliant

