



Rapid Fiber™ Faceplate, pull & click SC/APC, 30 meters cable on spool, wall mount

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Faceplate kit
Product Brand	Rapid Fiber™
Product Series	RFP

General Specifications

Color	White
Cover Type	Hinged with latches
Interface Type	SC/APC
Mounting	Wall mount
Port Capacity, maximum	2
Total Ports, quantity	1

Dimensions

Height	74.93 mm 2.95 in
Width	115.062 mm 4.53 in
Cable Length	30 m 98.425 ft
Depth	52.07 mm 2.05 in
Cable Diameter	1 mm 0.039 in

Material Specifications

Material Type	LSZH Thermoplastic
----------------------	--------------------

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

260103729 | RFP-130S41LW-CS

Fiber Type G.657.B3

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

