C96541-000 | OCC1D-X-550-NNNQF



OCC1D DWDM, 1 channel, double demux, 1533.47 nm starting wavelength, 0.250 mm cable, light duty housing, field installable

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type DWDM component

Product Series OCC1D

General Specifications

Device Type Component, rectangular

Functionality Demultiplexing

Technology Type Thin film filter (TFF)

Application For use in FOSC closures

Circuits, quantity 2

Distribution Type 1-channel DWDM

Interface, InputStub tailInterface, OutputStub tail

Multiplexers, quantity 2

Dimensions

Pigtail Length, Input2.5 m | 8.202 ftPigtail Length, Output2.5 m | 8.202 ftPigtail Diameter0.25 mm | 0.01 in

Optical Specifications

Starting Wavelength 1,533.47 nm

Packaging and Weights



C96541-000 | OCC1D-X-550-NNNQF

Packaging quantity

1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

