



Metal in-ground root, upon which the cabinet can be placed. This 300 mm in-ground root is typically used when no concrete base is available.

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Fiber cross-connect hub
<b>Product Series</b>	OCAB

## General Specifications

<b>Color</b>	Light Gray (RAL 7035)
--------------	-----------------------

## Dimensions

<b>Height</b>	300 mm   11.811 in
<b>Width</b>	800 mm   31.496 in
<b>Depth</b>	320 mm   12.598 in

## Material Specifications

<b>Finish</b>	Powder coated polyester
<b>Material Type</b>	Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Packaging Type</b>	Pallet
<b>Note</b>	No cover plates included - shall be ordered separately

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

