



Metal in-ground root, upon which the cabinet can be placed. This 300 mm in-ground root is typically used when no concrete base is available.

Product Classification

Regional Availability	EMEA
Product Type	Fiber cross-connect hub
Product Series	OCAB

General Specifications

Color	Olive-Green (RAL 6014)
--------------	------------------------

Dimensions

Height	300 mm 11.811 in
Width	800 mm 31.496 in
Depth	320 mm 12.598 in

Material Specifications

Finish	Powder coated polyester
Material Type	Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

Packaging and Weights

Included	Mounting hardware
Packaging Type	Pallet
Note	No cover plates included - shall be ordered separately

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

