

# CT-5-TUW-43-16



5 dB, Tapper, 340 – 6000 MHz

## Product Classification

**Regional Availability** Asia | Australia/New Zealand | EMEA | Latin America | North America

**Product Type** Tapper

## General Specifications

**Device Type** Tapper

**Application** Indoor/Outdoor

**Color** White

**Inner Contact Plating** Silver

**Interface** 4.3-10 Female

**Outer Contact Plating** Trimetal

## Dimensions

**Height** 25 mm | 0.984 in

**Width** 43 mm | 1.693 in

**Length** 141 mm | 5.551 in

## Electrical Specifications

**3rd Order IMD** -165 dBc

**3rd Order IMD Test Method** Two +43 dBm carriers

**Insertion Loss at Frequency Band** 1.8 dB @ 340–960 MHz | 1.95dB @ 3500-4500MHz | 1.95dB @ 4900-6000MHz | 2.1 dB @ 1695-2700MHz

**Return Loss at Frequency Band** 16.5dB @ 3500–4500MHz | 17.7 dB @ 4900–6000 MHz | 17.7dB @ 340–960MHz | 20.8 dB @ 1695–2700 MHz

**Average Power, maximum** 200 W

**Coupling** 5 dB

**Coupling Tolerance** +0.15/-0.6dB @ 698-960MHz | +0.2/-1.7dB @ 3500-4500MHz | +0.3/-0.8dB @ 4900-6000MHz | +0/-1.3dB @ 340-380 MHz | -0.2/-1.1dB @ 380-520 MHz | ±0.6dB @ 1695-2700 MHz

# CT-5-TUW-43-16

---

<b>Impedance</b>	50 ohm
<b>Operating Frequency Band</b>	1695 – 2700 MHz   340 – 960 MHz   3500 – 4500 MHz   4900 – 6000 MHz
<b>Peak Power, maximum</b>	3 kW
<b>Reflected Power, maximum</b>	200 W

## Mechanical Specifications

<b>Coupling Nut Proof Torque</b>	7 N-m   61.955 in lb
----------------------------------	----------------------

## Environmental Specifications

<b>Operating Temperature</b>	-35 °C to +85 °C (-31 °F to +185 °F)
<b>Relative Humidity</b>	Up to 100%
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP67

## Packaging and Weights

<b>Height, packed</b>	40 mm   1.575 in
<b>Width, packed</b>	90 mm   3.543 in
<b>Length, packed</b>	180 mm   7.087 in
<b>Weight, gross</b>	0.3 kg   0.661 lb
<b>Weight, net</b>	0.25 kg   0.551 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

