T-50-UW-43-M



Termination Load, 0-6000 MHz

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Termination Load

General Specifications

Device TypeTermination LoadApplicationIndoor/Outdoor

ColorBlackInner Contact PlatingSilver

Interface 4.3-10 Male
Outer Contact Plating Trimetal

Dimensions

 Height
 50 mm | 1.969 in

 Width
 50 mm | 1.969 in

 Length
 125 mm | 4.921 in

Electrical Specifications

Average Power, maximum 50 W Impedance 50 ohm


Operating Frequency Band 0 – 6000 MHz

VSWR 1.2

Derating Curve



T-50-UW-43-M



Environmental Specifications

Operating Temperature $-25 \,^{\circ}\text{C} \text{ to } +50 \,^{\circ}\text{C} \, (-13 \,^{\circ}\text{F to } +122 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

Ingress Protection Test Method IEC 60529:2001, IP65

Packaging and Weights

 Height, packed
 58 mm | 2.283 in

 Width, packed
 78 mm | 3.071 in

 Length, packed
 158 mm | 6.22 in

 Weight, gross
 0.42 kg | 0.926 lb

 Weight, net
 0.37 kg | 0.816 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



T-50-UW-43-M





