



M60 Computer Information Outlet Icon Insert, ivory

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Icon kit

General Specifications

Color Ivory

Material Specifications

Material Type High-impact, flame retardant, thermoplastic

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 25

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

107296535 | M60C-246

UK-ROHS

Compliant

