# 760235250 | COWO-S102



### COWO Customer Wall Outlet, 2 SC/UPC ports, no pigtails

- Allows easy and unobtrusive termination of fiber optic cables in an office, home or communications room
- Very flat design, mounts on a standard flush mount electrical outlet
- Possibility to invert the adapter in the holder to prevent disconnection when pulling the patch cords

### **Product Classification**

Regional AvailabilityEMEAProduct TypeOutletProduct SeriesCOWO

### General Specifications

**Color** White

**Cover Type** Hinged with latches

Interface Type SC/UPC

Lock Type Lead-wire seal | Screw

**Mounting** Wall mount

Splices Included, quantity 0

Total Ports, quantity 2

#### Dimensions

 Height
 115.062 mm | 4.53 in


 Width
 80.01 mm | 3.15 in

 Depth
 24.384 mm | 0.96 in

## Outline Drawing



## 760235250 | COWO-S102



## Material Specifications

Material Type LSZH thermoplastic

Optical Specifications

**Fiber Mode** Singlemode

## **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \text{ (-40 }^{\circ}\text{F to } +158 \,^{\circ}\text{F)}$ 

Environmental Space Indoor

## Packaging and Weights

Packaging quantity 1

## Regulatory Compliance/Certifications

Classification

<i>5</i> ,	
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Agency

**COMMSCOPE®** 

# 760235250 | COWO-S102

### Included Products

CY7021-000 - COWO Customer Wall Outlet, empty, for holding up to 2

COWO-NN00 adapters

## CY7021-000 | COWO-NN00



### COWO Customer Wall Outlet, empty, for holding up to 2 adapters

- Allows easy and unobtrusive termination of fiber optic cables in an office, home or communications room
- Very flat design, mounts on a standard flush mount electrical outlet
- Possibility to invert the adapter in the holder to prevent disconnection when pulling the patch cords

### **Product Classification**

Regional AvailabilityEMEAProduct TypeOutletProduct SeriesCOWO

### General Specifications

**Color** White

**Cover Type** Hinged with latches

Interface Type Unloaded

Lock Type Lead-wire seal | Screw

**Mounting** Wall mount

Port Capacity, maximum 4
Splices Included, quantity 0
Total Ports, quantity 0

#### Dimensions

 Height
 115.062 mm | 4.53 in


 Width
 80.01 mm | 3.15 in

 Depth
 24.384 mm | 0.96 in

### Outline Drawing



# CY7021-000 | COWO-NN00



## Material Specifications

Material Type LSZH thermoplastic

Optical Specifications

**Fiber Mode** Singlemode

## **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

Environmental Space Indoor

## Packaging and Weights

Packaging quantity

## Regulatory Compliance/Certifications

Classification

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

UK-ROHS Compliant



Agency

COMMSCOPE®

# CY7021-000 | COWO-NN00

