760235250 | COWO-S102



COWO Customer Wall Outlet, 2 SC/UPC ports, no pigtails

- Allows easy and unobtrusive termination of fiber optic cables in an office, home or communications room
- Very flat design, mounts on a standard flush mount electrical outlet
- Possibility to invert the adapter in the holder to prevent disconnection when pulling the patch cords

Product Classification

Regional AvailabilityEMEAProduct TypeOutletProduct SeriesCOWO

General Specifications

Color White

Cover Type Hinged with latches

Interface Type SC/UPC

Lock Type Lead-wire seal | Screw

Mounting Wall mount

Splices Included, quantity 0

Total Ports, quantity 2

Dimensions

 Height
 115.062 mm | 4.53 in


 Width
 80.01 mm | 3.15 in

 Depth
 24.384 mm | 0.96 in

Outline Drawing



760235250 | COWO-S102



Material Specifications

Material Type LSZH thermoplastic

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Environmental Space Indoor

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Classification

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

ROHS Compliant UK-ROHS Compliant



Agency

COMMSCOPE®

760235250 COWO-S102

Included Products

COWO Customer Wall Outlet, empty, for holding up to 2 CY7021-000 COWO-NN00

adapters

