

Rapid Fiber™ Faceplate, SC/APC, no spool, wall mount



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Faceplate kit
Product Brand	Rapid Fiber™
Product Series	RFP

General Specifications

Cover Type	Press fit
Interface Type	Internal SC/APC through adapter
Mounting	Wall mount
Port Capacity, maximum	2
Total Ports, quantity	0

Dimensions

Height	74.93 mm 2.95 in
Width	115.062 mm 4.53 in
Depth	14.986 mm 0.59 in

Material Specifications

Material Type	LSZH Thermoplastic
----------------------	--------------------

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

CV5880-001 | RFP-0-00-S2-1-L-X-X-TM

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

