# CV6986-000 | HFTP-NO-L102-E



HFTP Customer premises fiber wall outlet, LC/UPC, no pigtails, two duplex adapters

- Compact fiber wall outlet for use at the final fiber termination point in the customer premises
- Can be wall mounted and mounted on wall boxes with fixation points of 60mm
- Direct termination with field installable connectors
- Laser safe with in-built individual shutters

#### **Product Classification**

Regional Availability EMEA
Product Type Outlet
Product Series HFTP
Minimum Order Quantity 300

# General Specifications

ColorWhiteCover TypeScrew-onInterface TypeLC/UPCMountingWall mount

Total Ports, quantity 2

#### Dimensions

 Height
 105.41 mm | 4.15 in


 Width
 82.55 mm | 3.25 in


 Depth
 23.876 mm | 0.94 in

### Outline Drawing



# CV6986-000 | HFTP-NO-L102-E





### Material Specifications

Material Type LSZH thermoplastic

**Optical Specifications** 

**Fiber Mode** Singlemode

# **Environmental Specifications**

Storage Temperature -30 °C to +60 °C (-22 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

Environmental Space Indoor

### Packaging and Weights

Packaging quantity 10

# Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

**COMMSCOPE®** 

# CV6986-000 | HFTP-NO-L102-E



# Included Products

CK7246-000 HFTP-N0-NN00-E HFTP Customer premises fiber wall outlet, no adapters, no pigtails, for splicing only

**COMMSCOPE®**