

# BN-918710

---



3-1/8 EIA Coupling Element, O-Ring, screw-set

## Product Classification

**Product Type** Coupling element

## General Specifications

**Inner Contact Plating** Silver

**Interface** 3-1/8 in EIA Flange

## Dimensions

**Height** 81.3 mm | 3.201 in

**Width** 81.3 mm | 3.201 in

**Length** 101.1 mm | 3.98 in

## Electrical Specifications

**Connector Impedance** 50 ohm

**Operating Frequency Band** 1 – 5200 MHz

## Environmental Specifications

**Attenuation, Ambient Temperature** 20 °C | 68 °F

**Average Power, Ambient Temperature** 20 °C | 68 °F

**Average Power, Inner Conductor Temperature** 100 °C | 212 °F

## Packaging and Weights

**Included** O-rings | Screw set

**Weight, net** 500 g | 1.102 lb

## Regulatory Compliance/Certifications

# BN-918710

---

## Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS



## Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant