

BN-919310



6-1/8 EIA Coupling Element, O-Ring, screw-set

Product Classification

Product Type Coupling element

General Specifications

Inner Contact Plating Silver

Interface 6-1/8 in EIA Flange

Dimensions

Height 153.7 mm | 6.051 in

Width 153.7 mm | 6.051 in

Length 106.6 mm | 4.197 in

Electrical Specifications

Connector Impedance 50 ohm

Operating Frequency Band 1 – 5200 MHz

Environmental Specifications

Attenuation, Ambient Temperature 20 °C | 68 °F

Average Power, Ambient Temperature 20 °C | 68 °F

Average Power, Inner Conductor Temperature 100 °C | 212 °F

Packaging and Weights

Included O-rings | Screw set

Weight, net 800 g | 1.764 lb

Regulatory Compliance/Certifications

BN-919310

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS



Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant