FGS-MH4E-B



FiberGuide® 45° Horizontal Elbow, 4x6in, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Elbow

Product Brand FiberGuide®

Product Series FGS

General Specifications

Angle/Bend Direction 45°

Color Yellow

Orientation Horizontal

Section Type Elbow section

Dimensions

 Height
 112 mm | 4.409 in

 Width
 152 mm | 5.984 in


 Length
 259 mm | 10.197 in

System Dimensions 102 mm x 152 mm (4 in x 6 in)


Ordering Tree



FGS-MH4E-B



Section Color



* Support brackets only come in black

Section Size

10	Α	4 x 4 in
	В	4 x 6 in
	F	4 x 12 in
	G	2 x 6 in
	Н	4 x 24 in
	H-VS	4 x 24 in, variable support bracket

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 0.45 kg | 0.992 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

