FGS-MH9E-F



FiberGuide® 90° Horizontal Elbow, 4x12in, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Elbow

Product Brand FiberGuide®

Product Series FGS

General Specifications

Angle/Bend Direction 90°

Color Yellow

Orientation Horizontal

Section Type Elbow section

Dimensions

 Height
 112 mm | 4.409 in

 Width
 347 mm | 13.661 in


 Length
 440 mm | 17.323 in

System Dimensions 102 mm x 305 mm (4 in x 12 in)

Ordering Tree



FGS-MH9E-F



Section Color

9	empty	yellow
	В	black

^{*} Support brackets only come in black

Section Size

1	А	4 x 4 in
0	В	4 x 6 in
	F	4 x 12 in
	F-VS	4 x 12 in , variable support bracket
	G	2 x 6 in
	М	4 x 18 in

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 1.38 kg | 3.042 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

