
# FGS-MSHS-CB



FiberGuide® Vertical Straight Section with 1.5in Slot Spacing, Rounded Opening, 2x2in, Yellow

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Slotted vertical
Product Brand	FiberGuide®
Product Series	FGS

## General Specifications

Product Feature	Slotted
Color	Yellow
Orientation	Vertical
Section Type	Straight Section
Dimensions	
Height	50.8 mm   2 in
Width	50.8 mm   2 in
Length	1829 mm   72.008 in
System Dimensions	51 mm x 51 mm (2 in x 2 in)

## Ordering Tree

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 9, 2023



# FGS-MSHS-CB

yellow

black

6 ft

10 ft 12 ft



#### **Section Color**

Section Length

empty

9

11

Section Size

011 5120	
А	4 x 4 in
В	4 x 6 in
С	2 x 2 in
D	4 x 4 in, slotted duct, 2 in slot spacing
	4 x 12 in
F-CF	4 x 12 in, with center divider
G	2 x 6 in
Н	4 x 24 in
К	2 x 4 in, slotted duct, 2 in slot spacing
STOR-B	4 x 6 in, with slack storage spools
STOR-G	2 x 6 in, with slack storage spools
STOR-F	4 x 12 in, with slack storage spools
	B C D F F-CF G H K K STOR-B

## Material Specifications

Material Type

Engineering Thermoplastic

## **Environmental Specifications**

Flammability Rating	CSA S143   UL 2024   UL 94 V-0
Halogen Characteristics	Blue Angel   TCO '99   WEEE
Safety Standard	CSA   UL

### Packaging and Weights

**Weight, net** 0.714 kg | 1.574 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 9, 2023



Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 9, 2023

