

CZ1836-000 | OCC1P-20400-S2SESEB



OCC1P Wideband Splitter, planar, singlemode, 2x4, symmetrical split ratio, SC/APC, 0.9 mm cable, medium duty housing

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Splitter component
Product Series	OCC1P

General Specifications

Device Type	Component, rectangular
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use in FOSS closures
Circuits, quantity	1
Distribution Type	2 x 4 splitter
Interface, Input	SC/APC
Interface, Output	SC/APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Pigtail Length, Input	1.5 m 4.921 ft
Pigtail Length, Output	1.5 m 4.921 ft
Pigtail Diameter, Input	0.9 mm 0.035 in
Pigtail Diameter, Output	0.9 mm 0.035 in

Environmental Specifications

Qualification Standards

Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

