

RPBS wraparound delivery sleeve heat shrink kit, pressurized, for 70 to 100 mm cable diameter, 250 mm sheet opening



- Combines an improved application method for standard resin blocking compounds with the advantages of the wraparound heat-shrinkable sleeve
- Used with suitable commercially available resins, the system forms a pressure block for the whole pressurized cable range

## OBSOLETE

This product was discontinued on: [September 20, 2021](#)

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Heat shrink delivery sleeve
<b>Product Series</b>	RPBS

## General Specifications

<b>Color</b>	Black
<b>Sealant Type</b>	Hotmelt adhesive

## Dimensions

<b>Height</b>	435 mm   17.126 in
<b>Length</b>	600 mm   23.622 in
<b>Expanded Inside Diameter, minimum</b>	100 mm   3.937 in
<b>Recovered Inside Diameter, maximum</b>	70 mm   2.756 in
<b>Single Cable Diameter, maximum</b>	100 mm   3.937 in
<b>Single Cable Diameter, minimum</b>	70 mm   2.756 in

## Material Specifications

<b>Material Type</b>	Fiber-reinforced multi-layer sealing sleeve
----------------------	---------------------------------------------

## Environmental Specifications

# 945152-000 | RPBS-C-I-100/70-250

---

**Environmental Space** Buried | Ducted

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Bag | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

