



Black 2 in PVC Tape, 20 ft

## Product Classification

|                      |                              |
|----------------------|------------------------------|
| <b>Product Type</b>  | Weatherproofing tape         |
| <b>Product Brand</b> | HELIAX®                      |
| <b>Ordering Note</b> | ANDREW® non-standard product |

## General Specifications

|                             |   |
|-----------------------------|---|
| <b>Application</b>          | Provides additional moisture seal for cable connections                                     |
| <b>Applications per Kit</b> | Four 1/2 in–1/2 in   Four 1/2 in–7/8 in to device   One 1/2 in–2-1/4 in   Two 1/2 in–7/8 in |
| <b>Color</b>                | Black   |

## Dimensions

|                     |   |
|---------------------|---|
| <b>Width</b>        | 50.8 mm   2 in  |
| <b>Length</b>       | 6096 mm   240 in  |
| <b>Nominal Size</b> | 1-1/4 in   1-5/8 in   1/2 in   1/4 in   2-1/4 in   3/8 in   5/8 in   7/8 in |

## Material Specifications

|                      |          |
|----------------------|----------|
| <b>Material Type</b> | PVC tape |
|----------------------|----------|

## Environmental Specifications

|                                       |  |
|---------------------------------------|--|
| <b>Operating Temperature</b>          | -10 °C to +80 °C (+14 °F to +176 °F)       |
| <b>UV Resistance Test Method</b>      | PVC tape test method UL 510, ASTM D1000    |
| <b>Weather Resistance Test Method</b> | 04AS00-03.6.0   MIL-STD-1344A, Method 1002 |

## Packaging and Weights

|                       |                  |
|-----------------------|------------------|
| <b>Height, packed</b> | 63.5 mm   2.5 in |
| <b>Width, packed</b>  | 63.5 mm   2.5 in |
| <b>Length, packed</b> | 50.8 mm   2 in   |

# 9905-71

---

**Packaging quantity** 1  
**Weight, gross** 0.08 kg | 0.176 lb

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |