

244106A-70



Flex-Twist Hanger Assembly for WR137

Product Classification

Product Type Hanger kit

General Specifications

Cable Type Elliptical waveguide

Cables per Hanger 1

Color Silver

Hanger Type Flex-Twist hanger

Mounting 4.5 in OD pipe

Dimensions

Waveguide Size WR137 | WG14 | R70

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Wind Speed, survival with 1/2 in (12 mm) radial ice 201.167 km/h | 125 mph

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Test Method MIL-F-14072C | MIL-STD-889B

Packaging and Weights

Included Clamp | Rubber grommet | Threaded rod

Packaging quantity 1

Regulatory Compliance/Certifications

Agency **Classification**

244106A-70

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

