

Cold shrink Kit for 16 mm (0.62 in) to 10.54 mm (0.41 in) connections

Product Classification

 Product Type
 Cold shrink kit

 Product Brand
 HELIAX®

Ordering Note ANDREW® non-standard product

General Specifications

Application Provides additional moisture seal for cable connections

Color Black

Dimensions

Length 202.946 mm | 7.99 in

Cable Diameter for Seal, maximum16 mm | 0.63 in

Cable Diameter for Seal, minimum10.54 mm | 0.415 in

Inner Diameter 53.09 mm | 2.09 in

Material Specifications

Material Type EPDM rubber

Environmental Specifications

UV Resistance Test MethodUV condensation reference ASTM-G-53, light source UVA 340 fluorescent

lamp

UV Resistance, minimum with no degradation ≥1000 hours

Weather Resistance Test Method 04AS00-03.6.0 | IEC 60529:2001, IP67 | MIL-STD-1344A, Method 1002

Packaging and Weights

Height, packed 299.72 mm | 11.8 in

Width, packed $76.2 \, \mathrm{mm}$ | 3 inLength, packed $76.2 \, \mathrm{mm}$ | 3 in



245173

Included One EPDM rubber tube | Two sealing foam strips

Packaging quantity 1

Weight, gross 0.14 kg | 0.309 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

