26985A

Lace-up Hoisting Grip for 3 in coaxial cable and elliptical waveguide 28 and 34

OBSOLETE

Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m | 200 ft
Cable Type	Corrugated | Elliptical waveguide
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	762 mm | 30 in
Leader Length, minimum	457.2 mm | 18 in
Nominal Size	3 in
Waveguide Size	WR229 | WG11 | R40

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Tin-coated bronze

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 27, 2023

26985A

Mechanical Specifications

Pull Load Capacity	226.796 kg | 500 lb

Packaging and Weights

Packaging quantity	1
Weight, gross	1.43 kg | 3.153 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 27, 2023