

29958-C



Lace-up Hoisting Grip for 5/8 in coaxial cable, elliptical waveguide 85, 90, 127, 132 PWRT-608 and PWRT-606. Kit also includes 2 inch tape roll. .

Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® standard product (Global)

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	508 mm 20 in
Leader Length, minimum	152.4 mm 6 in
Nominal Size	5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	226.796 kg 500 lb
---------------------------	---------------------

Packaging and Weights

Height, packed	55.88 mm 2.2 in
Width, packed	236.22 mm 9.3 in

29958-C

Length, packed	236.22 mm 9.3 in
Packaging quantity	1
Weight, gross	0.3 kg 0.661 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

