

Lace-up Hoisting Grip for 5 in coaxial cable



OBSOLETE

Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Cable Type	Corrugated
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	1397 mm 55 in
Leader Length, minimum	304.8 mm 12 in
Nominal Size	5 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Tin-coated bronze
---------------	-------------------

Mechanical Specifications

31031-1

Pull Load Capacity 226.796 kg | 500 lb

Packaging and Weights

Packaging quantity 1
Weight, gross 3.05 kg | 6.724 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

