## 437160-000 | T-DUX-75



#### TDUX - Inflatable Duct Seal, size 75

- Flexible and reliable wraparound inflatable sealing system for cables
- Fast and easy to install or remove, even when water is flowing out of the duct
- Independent of duct or cable ovality
- Water and airtight up to 50 kPa (7 psi)
- Environmentaly friendly, non-toxic and resistant to chemicals

#### **Product Classification**

Regional Availability Latin America | North America

Product Type Cable duct seal

Product Series TDUX

Ordering Note When sealing more than two cables in a duct, seperate orderable TDUX-CL clips are to be

used

#### **Dimensions**

Width 120 mm | 4.724 in

Length 332 mm | 13.071 in

Cable Diameter, maximum 56 mm | 2.205 in

Cable Diameter, minimum 28 mm | 1.102 in


Conduit Inner Diameter, maximum 75 mm | 2.953 in

Conduit Inner Diameter, minimum 55 mm | 2.165 in

### Dimension Drawing



# 437160-000 | T-DUX-75



### **Environmental Specifications**

Installation temperature -5 °C to +40 °C (+23 °F to +104 °F)

Packaging and Weights

**Included** Inflatable bladder with sealing mechanism

Packaging quantity 10

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

