CGT158



Connector Grounding Kit for Mounting Rail for 1-5/8 in connectors

OBSOLETE

This product was discontinued on: September 30, 2012

Product Classification

Product Type	Grounding kit
Ordering Note	CommScope® non-standard product

General Specifications

Cable Type	Corrugated
Grounding Kit Type	Connector Grounding Kits
Thread Size	3/8 in | M10

Dimensions

Nominal Size	1-5/8 in

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)

Packaging and Weights

Height, packed	152.4 mm | 6 in
Width, packed	203.2 mm | 8 in
Length, packed	25.4 mm | 1 in
Included	3/8 in hardware | One 3/8 channel nut with spring | One aluminum channnel

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 9, 2023

CGT158

Packaging quantity	1
Weight, gross	0.27 kg | 0.595 lb

Regulatory Compliance/Certifications

Agency	**Classification**
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 9, 2023