

# CM-R78

---



## Round Chimney Mount, 7–8 ft OD

Allows for standard sector frame to be mounted to a chimney utilizing (2) "760258156-001" interface brackets per sector frame. Ordered separate.

Sector frames ordered separate.

Site engineer of record to determine capacity and structure suitability for installation.

### Product Classification

<b>Product Type</b>	Chimney mount
<b>Ordering Note</b>	ANDREW® non-standard product
<b>Warranty</b>	One year

### General Specifications

<b>Mounting</b>	Round Chimneys, 2.13–2.44 m (7–8 ft) OD
-----------------	---

### Dimensions

<b>Height</b>	609.6 mm   24 in
<b>Width</b>	1524 mm   60 in
<b>Length</b>	1524 mm   60 in

### Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

### Mechanical Specifications

<b>Wind Rating</b>	For Specifications, please contact your local ANDREW representative
<b>Wind Rating Test Method</b>	TIA/EIA-222

### Packaging and Weights

# CM-R78

---

**Included** Brackets | Hardware

**Packaging quantity** 1

**Weight, net** 136.1 kg | 300.049 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Warranty**

For more information, please consult our Product Warranty guidelines

**Wind Rating**

BWS—Base Wind Speed; FBC—Florida Building Code