

L4SGRIP



Support Hoisting Grip with clamp for 0.62-0.74 in (15.7-18.7 mm) coaxial cable

Product Classification

Product Type	Hoisting grip
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Support hoisting grip
Installation Tool	Required, not included
Support Clamp	Included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	254 mm 10 in
Leader Length, minimum	177.8 mm 7 in
Compatible Diameter, maximum	18.7 mm 0.736 in
Compatible Diameter, minimum	15.7 mm 0.618 in
Nominal Size	1/2 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	226.796 kg 500 lb
---------------------------	---------------------

L4SGRIP

Packaging and Weights

Height, packed	170.18 mm 6.7 in
Width, packed	78.74 mm 3.1 in
Length, packed	279.4 mm 11 in
Packaging quantity	1
Weight, gross	0.3 kg 0.661 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

