


# FPCA-MMYZ



Fiber Optic Patch Cord, singlemode, 1.2 mm LSZH jacket, LC/APC-LC /APC, yellow

- 1.2 mm diameter cable provides a 65% space savings over commonly used 2.0 mm cable
- 1.2 mm diameter fiber patch cords use Reduced Bend Radius (RBR) fiber cable
- Typically used in environments where space constraints and cable routing prove most challenging
- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

<b>Regional Availability</b>	Europe   Latin America   Middle East/Africa   North America
<b>Product Type</b>	Fiber patch cord, simplex
<b>Product Series</b>	FPCA
<b>Government Funding</b>	Build America Buy America (BABA) compliant*

## General Specifications


<b>Connector A, quantity</b>	1
<b>Color, boot A</b>	Green
<b>Color, connector A</b>	Green
<b>Connector B, quantity</b>	1
<b>Color, boot B</b>	Green
<b>Color, connector B</b>	Green
<b>Interface, Connector A</b>	LC/APC
<b>Interface Feature, connector A</b>	Angled
<b>Interface, Connector B</b>	LC/APC
<b>Interface Feature, connector B</b>	Angled
<b>Jacket Color</b>	Yellow
<b>Total Fibers, quantity</b>	1

## Dimensions

<b>Diameter Over Jacket</b>	1.2 mm   0.047 in
-----------------------------	-------------------

# FPCA-MMYZ

## Ordering Tree



## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2/B2
<b>Insertion Loss, maximum, connector A</b>	0.34 dB
<b>Insertion Loss, maximum, connector B</b>	0.34 dB
<b>Return Loss, minimum, connector A</b>	65 dB
<b>Return Loss, minimum, connector B</b>	65 dB

## Environmental Specifications

<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>

# FPCA-MMYZ

---


ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted



## Included Products

760243025 – 1.2 mm LSZH Simplex Cable  
POC-FO-CAB-SX-8G-1.2MM-YL



1.2 mm LSZH Simplex Cable


## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor cable
<b>Product Series</b>	L-SP

## General Specifications

<b>Jacket Color</b>	Yellow
<b>Jacket Marking</b>	Custom printing
<b>Total Fiber Count</b>	1

## Representative Image



## Environmental Specifications

<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Cca
---	-----

<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s1a
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d0
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a2

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

