

760250656 | FIST-RSKG-1-SIL



FIST Gel Sealing Kit for round splice closure port, sealing 1 cable with diameter between 11 and 14 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

Product Classification

| | |
|------------------------------|---|
| Regional Availability | EMEA |
| Product Type | Gel sealing kit |
| Product Series | FIST-GC02 |
| Ordering Note | Cable jackets containing flame retardant components are advised to be combined with the Silicone gel multi-out seal |

General Specifications

| | |
|--------------------------------|---------------------------------------|
| Application | For use with FIST-GC02 Fiber closures |
| Cable Capacity, maximum | 1 |
| Color | Black |

Dimensions

| | |
|---------------------------------------|------------------|
| Single Cable Diameter, maximum | 14 mm 0.551 in |
| Single Cable Diameter, minimum | 11 mm 0.433 in |

Packaging and Weights

| | |
|---------------------------|---|
| Included | Cable termination brackets Dummy plugs Multi-out gel seal |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|---|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |

UK-ROHS

Compliant/Exempted

