SHK-78-3-P



Single Hanger Kit for 7/8 in coaxial cable, triple stack; includes hardware and angle adapter

Product Classification

Product TypeHanger kitProduct BrandValuSite™

Ordering Note ANDREW® non-standard product

General Specifications

Cables per Hanger 3

Color Black

Hanger Type Composite clamp

Harmonized System (HS) Code 85366910 (Coaxial cable and other coaxial electric conductors)

Mounting M8 hardware

Dimensions

Maximum Stack Height 3

 Height
 152.4 mm | 6 in

 Width
 26.2 mm | 1.031 in

 Length
 60.2 mm | 2.37 in

Compatible Cable Diameter Range 26.7–28.2 mm

Compatible Diameter, maximum28.2 mm | 1.11 inCompatible Diameter, minimum26.7 mm | 1.051 in

Nominal Size 7/8 in

Electrical Specifications

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

Material Specifications

Material Type Engineered plastic | Stainless steel 304



SHK-78-3-P

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Corrosion Resistance, minimum with no degredation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 15 cm | 5.906 in

 Width, packed
 15 cm | 5.906 in

 Length, packed
 3 cm | 1.181 in

Included Angle adapter | Hardware

Packaging quantity

Weight, gross 0.45 kg | 0.992 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

