

SSH-158



SnapStak® Hanger for 1-5/8 in coaxial cable

Product Classification

Product Type	Hanger kit
Product Brand	SnapStak®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Cables per Hanger	1
Color	Silver
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Maximum Stack Height	2
Height	40.9 mm 1.61 in
Width	50.8 mm 2 in
Length	89.9 mm 3.539 in
Compatible Cable Diameter Range	49–51.1 mm
Compatible Diameter, maximum	51.1 mm 2.012 in
Compatible Diameter, minimum	49 mm 1.929 in
Nominal Size	1-5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

SSH-158

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

Packaging and Weights

Height, packed 22 cm | 8.661 in

Width, packed 15 cm | 5.906 in

Length, packed 14.4 cm | 5.669 in

Packaging quantity 10

Weight, gross 0.6 kg | 1.323 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power