

TW-78-EZFC



Torque Wrench for 7/8 in EZfit® connectors, 34 mm

Product Classification

Product Type	Wrench
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Application	Attaches connectors to coaxial cable
Calibration	6 mo
Tool Type	Torque wrench

Dimensions

Wrench Opening	34.036 mm 1.34 in
-----------------------	---------------------

Material Specifications

Material Type	Steel
----------------------	-------

Mechanical Specifications

Torque Tolerance	+5/-0
Torque Value	300.93 in lb 34.001 N-m

Packaging and Weights

Height, packed	299.72 mm 11.8 in
Width, packed	299.72 mm 11.8 in
Length, packed	106.68 mm 4.2 in
Packaging quantity	1
Weight, gross	2.19 kg 4.828 lb

Regulatory Compliance/Certifications

TW-78-EZFC

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

