


# TW-N10

---



Torque Wrench for coupling torque of Nex10 connectors, 11 mm opening

## Product Classification

<b>Product Type</b>	Wrench
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Application</b>	Torques Nex10 connectors
<b>Calibration</b>	6 mo
<b>Tool Type</b>	Torque wrench

## Dimensions

<b>Wrench Opening</b>	10.922 mm   0.43 in
-----------------------	---------------------

## Material Specifications

<b>Material Type</b>	Steel
----------------------	-------

## Mechanical Specifications

<b>Torque Tolerance</b>	-0/+2
<b>Torque Value</b>	13.32 in lb   1.505 N-m

## Packaging and Weights

<b>Height, packed</b>	284.48 mm   11.2 in
<b>Length, packed</b>	279.4 mm   11 in
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.89 kg   1.962 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
---------------	-----------------------

# TW-N10

---

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

