WB-K410-B



Safety Grated Waveguide Bridge Kit, 24 in x 10 ft, with four 13 ft 4 in direct burial posts

Product Classification

Product Type Waveguide bridge kit

General Specifications

Application Direct burial

Cable Runs, quantity 24
Pipe, quantity 4

Dimensions

 Height
 4064 mm | 160 in

 Width
 609.6 mm | 24 in


 Length
 3048 mm | 120 in

Pipe Length 4,053.84 mm | 159.6 in



WB-K410-B

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Caps | Channel | Hardware | Posts | Support brackets | Trapeze

Packaging quantity 1

Weight, net 270.4 kg | 596.129 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ANDREW® an Amphenol company

WB-K410-B

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

MF-130 – Direct Burial Pipe Column, 13 ft 4 in

WB-CS24-3 – Safety Grated Channel Support, 24 in wide for 3-1/2 in OD

pip€

WB-CY210 - Safety Grated Waveguide Bridge Channel, 24 in x 10 ft

WB-T24-3 - Trapeze Kit, triple tee, 24 in wide, three rungs

