760243083 | FST-T2-0610-A0500F



FST-T2 Flexible Service Terminal, 12f, 6 Port x 2 Fiber, 6 HMFOC Adapters (Jack/male/pinned, 2 fibers per adapter at drop side, Stub at feeder side, black, 500 ft/152 m

- Flexible Service Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Flexible structure allowing installation in constrained spaces
- Output adapter ports have 2 Fibers per port; input 12 Fiber cable stub 500 foot length

Product Classification

Regional Availability North America

Product Type Access terminal, with multi-fiber port

Product Series FST-T2

Minimum Order Quantity 1

General Specifications

Cable Type Dielectric - Loose Tube

Cable, quantity 7

Distribution Type 6 ports

Drop Port TypeHardened multi-fiber (HMFOC) adapter

Drop Port, quantity 6

Enclosure Color Black

Mounting Handhole | Pedestal

Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Port, quantity 6

Splitter, quantity 0

Stub Type Stub tail

Dimensions

 Height
 112.5 mm | 4.429 in

 Width
 53 mm | 2.087 in

 Depth
 31 mm | 1.22 in


COMMSCOPE®

760243083 | FST-T2-0610-A0500F

Cable Length, stub 500 ft (152 m)

Cable Outer Diameter 4.1 x 7.6 mm (0.16 x 0.30 in)

Ordering Tree



Material Specifications

Enclosure Material Type Engineered plastic

Optical Specifications

Fiber Type G.657.A1/A2

Operating Wavelength Range 1310 – 1550 nm

Attenuation Single Ports, maximum 0.65 dB **Return Loss, Connector, minimum** 65 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Relative Humidity 5%-100%, condensing

Environmental Space Above ground | Below ground | Buried

Qualification Standards | IEC 61300, 1 m waterhead | Telcordia GR-3120-CORE | Telcordia GR-3152-CORE

UV Resistance UV stabilized

COMMSC PE®

760243083 | FST-T2-0610-A0500F

Packaging and Weights

Included Mounting hardware

Packaging quantity

Packaging Type Box | Carton

Weight, without cable 0.23 kg | 0.507 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

