



HFTP-AM Customer premises fiber wall outlet, no pigtail, no adapter

- Compact fiber wall outlet for use at the final fiber termination point in the customer premises
- Direct termination with field installable connectors
- Laser safe with in-built individual shutters

Product Classification

Regional Availability	EMEA North America
Product Type	Fiber wall outlet
Product Series	HFTP
Minimum Order Quantity	300

General Specifications

Color	White
Cover Type	Screw-on
Interface Type	SC/APC
Mounting	Wall mount
Total Ports, quantity	1

Dimensions

Height	105.156 mm 4.14 in
Width	83.058 mm 3.27 in
Depth	25.146 mm 0.99 in

Material Specifications

Material Type	LSZH thermoplastic
----------------------	--------------------

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Relative Humidity	Up to 93%, non-condensing

760249281 | HFTP-AM-NN00-E

Environmental Space Indoor

Packaging and Weights

Packaging quantity 10